


la belle BC 421




la belle BC 421 the bone conductor glasses

- BTE-module for eyeglasses
- module cold bendable
- digital hearing-system
- 2 microphone technology with fixed or automatic directionality
- 4 programmes selected by push button
- 4-channel WDRC
- Dynamic Contrast Detection
- 12-band gain adjustment
- volume control VC
- telecoil
- MPO
- adaptive feedback cancellation (until -22dB)
- layered noise reduction
- programme tones and battery tones
- battery type 312
- colours: anthracite-black
- colour of chamber cap: silver, gold, anthracite
- feeler pin in support of finding the appropriate glasses

Technical data

		DIN IEC 118-9:1987
FOG for OSPL90	(dB)	124
gain max.	(dB)	52
Frequency range	(Hz)	200-5600
Operating current	(mA)	1,2
Equivalent input noise	(dB)	20

please turn over



Programming:

with Bruckhoff fitting software and Siemens programming cable (CONNEXX cable grey)

Technical change without prior notice