


la belle CL 410






la belle CL 410

- BTE-module for eyeglasses
- module cold bendable
- digital hearing system
- natural sound transfer via ex-speaker system *
- 4 programme selected by push button
- 4 channel WDRC
- Dynamic Contrast Detection
- 12-band gain adjustment
- MPO
- adaptive feedback cancellation (until -17dB)
- layered noise reduction
- programme tones and battery tones
- ideally suited to open ear application
- takes 312 type batteries
- replaceable cerumen defenser filter
- tube warm bendable
- colours: gold-brown, silver-black, anthracite-black
- mono, stereo, CROS, BiCROS
- *ex-speaker = speaker in the ear canal



Technical data			
		DIN EN 60118-0	DIN EN 60118-7
OSPL90 max.	(db)	119	112
Gain 50dB(FOG) max.	(dB)	52	43
Frequency range	(Hz)	200-6000	200-6500
Equivalent input noise	(dB)	22	22
Operating current	(mA)	1,2	1,2

please turn over



Before programming, please remove the device cover plate

Programming:

Bruckhoff fitting software and Siemens programming cable (CONNEXX cable grey)

Technical change without prior notice